

Product datasheet

Specifications



mobile generator XGR Vigilohm -
115..127 V AC 50/60 Hz - 2.5 mA
2.5 Hz

50281

Main

Range Of Product	Vigilohm
Device Short Name	XGR
Product Or Component Type	Locating signal generator
Earthing System	IT

Complementary

Type Of Installation To Be Monitored	500 V - DC (between poles) 0...760 V - AC at 45...400 Hz (device connected to neutral) 0...440 V - AC at 45...400 Hz (device connected to phase)
Auxiliary Supply Voltage	115/127 V - AC at 50/60 Hz
Output Frequency	2.5 Hz
Power Consumption In Va	15 VA
Measurement Current	2.5 mA
Internal Impedance	40 kOhm
Material	Plastic
Net Weight	0.85 kg
Height	59 mm
Width	108 mm
Depth	189 mm

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration