



PratiKa wander socket - straight -125 A - 3P + N + E - 480...500 V **AC - IP67** 

81498

! Discontinued on: 30 Jun 2023

! Discontinued

### Main

Range	PratiKa
Product Or Component Type	Wander socket
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

## Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	125 A
[Ue] Rated Operational Voltage	480500 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	7 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel
Connections - Terminals	Captive screws
Cable Cross Section	1670 mm²
Cable Outer Diameter	2648 mm
Cable Entry	Cable gland
Thread Type	Pg 48
Net Weight	1.72 kg
Height	131 mm
Width	131 mm
Depth	325 mm
Colour	Grey (RAL 7035)
Voltage Colour	Black

### **Environment**

Standards	IEC 60309-2 IEC 60309-1
Ip Degree Of Protection	IP67 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-1
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C ( 86400 s ) -2540 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.1 cm
Package 1 Width	13.1 cm
Package 1 Length	32.5 cm
Package 1 Weight	1.72 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration