Product datasheet

Specifications





PratiKa industrial socket - 16 A - 3P + E - 380...415 V AC - IP44

83108

() Discontinued on: 30 Jun 2023

(!) Discontinued

Main

Range	PratiKa
Product Or Component Type	Socket
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Wall-mounted
Plug, Socket, Control Station Shape	Angled
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	380415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel
Connections - Terminals	Captive screws, completely loosened
Cable Cross Section	14 mm ²
Cable Outer Diameter	815 mm
Net Weight	0.3 kg
Base Dimension	80 x 100 mm
Height	100 mm
Width	80 mm
Depth	155 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Standards	EN 60309-1 EN 60309-2
Ip Degree Of Protection	IP44 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C(86400 s)
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	12.8 cm
Package 1 Length	15.4 cm
Package 1 Weight	264.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	17.6 cm
Package 2 Width	26.4 cm
Package 2 Length	26.8 cm
Package 2 Weight	1.234 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	8
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm

Package 3 Length
Package 3 Weight

Contractual warranty

Warranty

18 months

40.0 cm

2.955 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Circularity Profile	No need of specific recycling operations
	Product out of China RoHS scope. Substance declaration for your information
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration