

# Product datasheet

Specifications



## PratiKa industrial plug - 32 A - 2P + E - 380...415 V AC - IP44

83519

⚠ Discontinued on: 12 Jan 2023

⚠ Discontinued

### Main

Range	PratiKa
Product Or Component Type	Plug
Device Short Name	PratiKa plug
Plug, Socket Category	Low voltage
Poles Description	2P + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Mounting Mode	Wall-mounted
Plug, Socket, Control Station Shape	Angled
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	380...415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	9 h
Plug, Socket Material	Self-extinguishing engineering polymer
Contacts Material	Pins: nickel plated brass
Connections - Terminals	Captive screws
Cable Cross Section	2.5...10 mm²
Cable Outer Diameter	11.5...21 mm
Net Weight	0.43 kg
Base Dimension	106 x 130 mm
Height	130 mm
Width	106 mm
Depth	130 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

### Environment

Standards	EN 60309-2 EN 60309-1
-----------	--------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ip Degree Of Protection</b>	IP44 conforming to IEC 60529
<b>Ik Degree Of Protection</b>	IK08 conforming to EN 62262
<b>Fire Resistance</b>	850 °C conforming to IEC 60695-2-1
<b>Relative Humidity</b>	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
<b>Operating Altitude</b>	2000 m
<b>Ambient Air Temperature For Operation</b>	35 °C ( 86400 s ) -25...40 °C

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------