


Product datasheet

Specifications



Kavacha -Surface Mount Door Bell with LED Indicator (White) IP44

A3031WBP_WE

Main

Range	Kavacha
Product Or Component Type	Bell press switch
Device Application	Residential
Colour Tint (Frame)	White

Complementary

Wiring Device Mounting	Surface
Local Signalling	LED (white)
Rated Current	6 A at 250 V AC
Width	74 mm
Height	124 mm

Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP44
Standards	IEC 60529 GB 16915.1 IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7 cm
Package 1 Length	12 cm
Package 1 Weight	122.55 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	17
Package 2 Height	13 cm
Package 2 Width	19 cm
Package 2 Length	25 cm
Package 2 Weight	1.88 kg
Unit Type Of Package 3	S04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	85
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	10.7 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information

Yes

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information