



## Acti9 remote indication iATLs

A9C15405

### Main

Range Of Product	Acti9
Device Short Name	iATLs
Product Or Component Type	Remote indication auxiliary
Signal Contacts Composition	1 C/O
Signalling Circuit Voltage	24 V AC/DC: 10 mA 12240 V AC: 50/60 Hz 6 A 1224 V DC: 6 A 15240 V AC: 50/60 Hz 2 A 1324 V DC: 2 A
[Uc] Control Circuit Voltage	24240 V AC 50/60 Hz 24240 V DC

### Complementary

[Ui] Rated Insulation Voltage	440 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Mounting Mode	Fixed, on right side of TL
Mounting Support	DIN rail
9 Mm Pitches	1
Height	81 mm
Width	9 mm
Depth	69 mm
Colour	White
Connections - Terminals	Tunnel type terminals0.54 mm² - rigid Tunnel type terminals0.54 mm² - rigid - with cable end Tunnel type terminals14 mm² - flexible Tunnel type terminals14 mm² - flexible - with cable end
Wire Stripping Length	11 mm
Tightening Torque	1 N.m
Range Compatibility	Acti 9 Acti9 iTL iTL Acti 9 Acti9 iTL iTLi Acti 9 Acti9 iTL iTLs Acti 9 Acti9 iTL iTLc Acti 9 Acti9 iTL iTLc Acti 9 Acti9 iTL iTLm
Product Compatibility	ITL (32 A) ITL (16 A)

#### **Environment**

Overvoltage Category

Ip Degree Of Protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2050 °C
Ambient Air Temperature For Storage	-4070 °C
Standards	EN/IEC 60669-2-2

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.1 cm
Package 1 Width	9.3 cm
Package 1 Length	7.7 cm
Package 1 Weight	40 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.6 cm
Package 2 Width	9.9 cm
Package 2 Length	26.5 cm
Package 2 Weight	531 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.267 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations