Product datasheet

Specification





Acti9 iPB 1NC single push button grey - indicator light red 110-230Vac

A9E18037

Main

Range Of Product	Acti9	
Product Name	Acti9 iPB	
Product Or Component Type	Push-button	
Device Short Name	iPB	
Standards	IEC 60947-5-1	

Complementary

Contacts Type And Composition	1 NC
[le] Rated Operational Current	20 A
[Ue] Rated Operational Voltage	250 V AC
Control Type	1 push-button grey
Local Signalling	LED indicator red, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Signalling Circuit Voltage	AC: 110230 V 50/60 Hz
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: Clario Upside: Librio Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical Durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - Terminals	Staggered tunnel terminal1 cable(s) 0.5 mm² rigid Staggered tunnel terminal1 cable(s) 0.5 mm² flexible Staggered tunnel terminal1 cable(s) 0.5 mm² flexible with ferrule Staggered tunnel terminal2 cable(s) 2.5 mm² rigid Staggered tunnel terminal2 cable(s) 2.5 mm² flexible Staggered tunnel terminal2 cable(s) 2.5 mm² flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	2.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	45.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	10.000 cm
Package 2 Length	23.000 cm
Package 2 Weight	599.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.972 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations