Product datasheet

Specification





Cable end, Linergy TR cable ends, twin conductor, blue, 2.5mm², for insulated cable, medium size, 5 sets of 50

AZ5DE025D

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-4
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 50
Cable Cross Section	2.5 mm²

Complementary

Cable End Type	Twin conductor
Additional Information	Without marker tag holder
Colour	Grey
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	2
Awg Gauge	AWG 14
Bezel Size	Ø 4.2 x 7.8 mm
Tube Diameter	3.2 mm
Length	18.5 mm
Tube Length	10 mm
Net Weight	0.145 kg

Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-20105 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Package 1 Weight	0.300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	250
Package 2 Height	13.000 cm
Package 2 Width	7.000 cm
Package 2 Length	12.600 cm
Package 2 Weight	135.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	2500
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.690 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
②	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
②	Halogen Free Plastic Parts Product

Certifications & Standards

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
	EU RoHS Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration