

Product datasheet

Specifications



BCPM 50 A split core CTs - set of 6 - 1.8 m lead lengths

BCPMSCCT0

Main

Range	PowerLogic
Product Or Component Type	Current transformer
Electrical Connection	Cable: 1.8 m300 V
[In] Rated Current	50 A

Complementary

Product Destination	BCPMSC
Current Transformer Type	Split core balance
Network Frequency	50/60 Hz
Quantity Per Set	Set of 6
Width	Internal: 10 mm External: 23 mm
Depth	26 mm
Height	Internal: 11 mm External: 40 mm

Environment

Ambient Air Temperature For Operation	0...60 °C
---------------------------------------	-----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	15.2 cm
Package 1 Length	21.8 cm
Package 1 Weight	500.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	