





# APC Back-UPS, 625VA, Floor, 230V, 3 Universal outlets, AVR

BX625CI-MS

### **Overview**

Lead Time Usually in Stock

### Main

Mani	
Main Input Voltage	230 V
Rated Power In W	325 W
Rated Power In Va	625 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Output Connection Type	3 universal receptacle
Cable Length	1.22 m
Number Of Cables	1
Battery Type	Lead-acid battery

## **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Number Of Battery Filled Slots	1
Number Of Battery Free Slots	0
Battery Recharge Time	6 h
Number Of Battery Replacement Quantity	1
Battery Charger Power	11 W rated
Battery Life	24 year(s)
Replacement Battery	APCRBC110 ☐
Extended Runtime	0

#### **General**

Provided Equipment	1, detachable 2.0 m NEMA 5-15P to IEC C13 power cord user manual
Product Web Sub-Family	Entry level
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

# **Physical**

Colour	Black
Height	07.05
neight	27.85 cm
Width	16 cm
Depth	8.85 cm
Net Weight	5 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

## Input

Network Frequency	4565 Hz
Input Voltage Limits	151299 V
Maximum Input Current	3 A
Switching Current Capacity	7 A
Input Protection Type	3-pole circuit breaker

# Output

Maximum Configurable Power In W	325 W
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised
Ups Type	Line interactive
Wave Type	Square wave
Efficiency	65.3 % (full load) 75.8 % (half load)
Maximum Configurable Power In Va	625 VA
Transfer Time	4 ms typical : 8 ms maximum

## Conformance

Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Equipment Protection Policy	No EPP for ASEAN

## **Environmental**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Ambient Air Temperature For Storage	-1540 °C
Storage Relative Humidity	095 %
Acoustic Level	45 dBA

## **Surge Protection and Filtering**

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	39.9 cm
Package 1 Width	12.8 cm
Package 1 Length	21.5 cm
Package 1 Weight	5.2 kg
Scc14	10731304308178

## **Contractual warranty**

16 May 2024

Warranty 2 years repair or replace

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

#### Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Mercury Free

Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information