

Product datasheet

Specifications



Kavacha - 13A - 250V - Surface Mount 1 Pole Switched Socket - IP56

CSC313_GY

Main

Range Of Product	Kavacha
Range	Kavacha
Product Or Component Type	Switched socket
Device Short Name	AS
Device Application	Power supply

Complementary

Wiring Device Mounting	Surface
Switch Function	1-pole
Rated Current	13 A at 250 V AC
Poles Description	1P
Width	80 mm
Height	160 mm
Depth	80 mm

Environment

Ip Degree Of Protection	IP56
Standards	BS 1363-2 IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	8.5 cm
Package 1 Length	18 cm
Package 1 Weight	333.333 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	27.7 cm
Package 2 Width	35.8 cm
Package 2 Length	35.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	10000 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	480
Package 3 Height	130 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	178000 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
