

Product datasheet

Specifications



20A 250V Surface Mount One Gang Double Pole Switch with Neon IP66

CSW220N_GY

Main

Range	Kavacha
Product Or Component Type	Switch
Device Short Name	AS
Device Application	Control
Colour Tint (Frame)	Grey

Complementary

Wiring Device Mounting	Surface
Switch Function	2-pole switch
Local Signalling	Indicator light, neon (red)
Rated Current	20 A at 250 V AC
Poles Description	2P
Number Of Gangs	1 gang

Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP66
Standards	IEC 60529 IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	8.4 cm
Package 1 Length	10.6 cm
Package 1 Weight	272.727 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	45
Package 2 Height	27.8 cm
Package 2 Width	36 cm
Package 2 Length	47 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	12000 g
------------------	---------