Product datasheet

Specifications





Cable end, Linergy TR cable ends, single conductor, white, 16mmÂ², medium size, for clip-in, 10 sets of 100

DZ5CA162

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Bag
Quantity Per Set	Set of 100
Cable Cross Section	16 mm²

Complementary

Cable End Type	Single conductor
Additional Information	For additional marker tag holder
Colour	White
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 6
Bezel Size	Ø 9.6 mm
Tube Diameter	6.2 mm
Length	24 mm
Tube Length	12 mm
Cad Overall Depth	24 mm
Net Weight	0.078 kg

Environment

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Package 1 Weight	0.600 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	4.000 cm
Package 2 Width	8.000 cm
Package 2 Length	12.000 cm
Package 2 Weight	66.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	6000
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.523 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
Ø	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
②	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations