Product datasheet

Specifications





S-Classic - switched socket outlet with neon - 1 gang - white

E15NR_WE

Main

Product Or Component Type	Switched socket
Outlet Poles Configuration	2P + E
Rated Current	13 A at 230 V AC 50 Hz
Quantity Per Set	Set of 1

Complementary

Device Presentation	Complete product
Number Of Gangs	1 gang
Pilot Light	Neon indicator
Device Mounting	Flush Surface
Material	Plate: PC (polycarbonate), white Dolly: PC (polycarbonate), white Base: PP (polypropylene), black
Embedding Depth	13.8 mm
Height	87 mm
Width	87 mm
Depth	29.3 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	BS 1363-2 SS 145-2 MS 589-2

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	9.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	76.0 g

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations