

Product datasheet

Specifications



13A Fused Connection Unit, Grey Silver

E3030FSG_GS

Main

Range	Neo
Product Or Component Type	Fused connection unit
Colour Tint	Grey silver
Standards	BS 1362-4

Complementary

Wiring Device Mounting	Flush Surface
Rated Current	13 A at 250 V AC 50 Hz
Contacts Material	Brass Phosphor bronze
Load Type	Resistive
Protection Type	Fuse
Material	Polycarbonate: grid plate Polycarbonate: surround
Number Of Cables	2 x 4 mm² input 1 x 1.5 mm² output 1 x 2.5 mm² output 3 x 0.5...1.5 mm² output 3 x 2.5 mm² input
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	8.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.7 cm
Package 1 Weight	137.5 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	100
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13.8 kg

Contractual warranty

Warranty	18 months
----------	-----------