# **Product datasheet**

Specifications

, Sreen Premium<sup>™</sup>



# Pieno - 2 x 2.1A USB Charger - Lavender Silver

E8232USB\_LS

#### Main

Range	Pieno
Product Or Component Type	USB charger
Fixing Mode	Screw

### Complementary

Device Mounting	Flush
Device Presentation	Mechanism
Colour Tint	Lavender silver
Surface Finish	Glossy
Surface Treatment	Untreated
Number Of Modules	2 modules 46 x 36.7 x 21.7 mm
Condition Of Use	Room temperature
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	1090 %
[Ue] Rated Operational Voltage	100/240 V AC 50/60 Hz
Integrated Connection Type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	PA (polyamide) 6: housing Silicone rubber: cover PC (polycarbonate): grid plate
Shape Of Screw Head	Cross
Number Of Terminals	2 screw terminals
Clamping Connection Capacity	<ul> <li>2.5 mm² for stranded cable(s)</li> <li>2.5 mm² for flexible cable(s)</li> <li>2.5 mm² for rigid cable(s)</li> <li>1.5 mm² for stranded cable(s)</li> <li>1.5 mm² for flexible cable(s)</li> <li>1.5 mm² for rigid cable(s)</li> </ul>
Wire Stripping Length	6 mm
Product Compatibility	Apple Major smart phone and tablet XiaoMi Samsung HW HTC

Power bank

Standards	CNS 13438 CNS 14336 GB 4943.1 IEC 60950-1 MS IEC 60950-1
Height	87 mm
Width	87 mm
Depth	39 mm
Embedding Depth	29.3 mm
Net Weight	0.1107 kg

#### Environment

Product Certifications	IEC CCC
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Liquid soap

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	117.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	936 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	9.36 kg

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information