Product datasheet

Specifications





13A Twin Gang Switched Socket with 2.1A USB, Lavender Silver

E82T25USB_LS_G2

Main

Range	Pieno	
Product Or Component Type	Power socket-outlet + USB charger	
Device Presentation	Mechanism	
Socket Additional Information	Shuttered	
Colour Tint	Lavender silver	
Load Type	No inductive load	

Complementary

Complementary	
Socket Number	1
Device Mounting	Flush 47 mm
Switch Function	ON/OFF power-socket outlet
Number Of Power Socket Outlets	2 x 2P + E with shutters, British
Rated Current	Power circuit: 13 A 220250 V, AC, 50/60 Hz
Surface Finish	Glossy
Surface Treatment	Painted
Number Of Gangs	2 gangs
Connector Type	USB type A
[Ue] Rated Operational Voltage	220250 V AC 50/60 Hz
Maximum Power Consumption In W	0.075 W
Input Power	16 W
Integrated Connection Type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	Polycarbonate: grid plate Polycarbonate: cover Polycarbonate: surround Polycarbonate: dolly Nylon + GF: shutter Brass: contact plate Steel: spring Nickel steel: terminal screw
Protection Type	USB port: over temperature protection with PWM IC circuit USB port: over voltage protection against surges with PWM IC circuit USB port: overcurrent between output phases and earth (on power up only) with PWM IC circuit
Shape Of Screw Head	Cross
Screwdriver Shape	Philips
Electrical Connection	3 screw terminal

10 May 2024

Clamping Connection Capacity	1 x 4 mm² for solid cable(s)
	2 x 4 mm² for stranded cable(s)
	1 x 2.5 mm ²
	2 x 2.5 mm²
Wire Stripping Length	1012 mm
Mounting Support	Mounting box conforming to BS 4662
Fixing Mode	By screws M3.5 x 25 mm
Fixing Center	120.6 mm
Product Compatibility	Smartphone
, ,	Apple
	HW
	HTC
	Tablet PC
	Samsung
	Power bank
	XiaoMi
Height	147 mm
Width	87 mm
Depth	38.6 mm
Embedding Depth	29.5 mm
Net Weight	0.166 kg

Environment

Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Standards	BS 1363-2 IEC 60950-1
Product Certifications	IEC
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	171.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	905.0 g

Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	21.0 cm
Package 3 Width	31.0 cm
Package 3 Length	50.0 cm
Package 3 Weight	8.55 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information