



Pieno - 115V/240V universal shaver Unit - vertical (WG)

E82T727V_WG

Main

Range Of Product	Pieno	
Product Or Component Type	Universal shaver	
Installation Direction	Vertical	
Input Voltage	240 V AC 50 Hz	
Output Voltage	115 V AC 50 Hz	
Transformer Rated Power In Va	20 VA	
Load Type	Polarised Non-polarised	

Complementary

Material	Polycarbonate: surround Polycarbonate: grid plate	
Width	147 mm	
Height	87 mm	
Depth	49.7 mm	

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	IEC 61558-2-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	9.4 cm
Package 1 Length	15.5 cm
Package 1 Weight	599.0 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations