# **Product datasheet**





## Auxiliary contact block, TeSys K, 2NO+2NC, front mounting, spring terminals

LA1KN223

### Main

Range	TeSys	
Product Name	TeSys K	
Product Or Component Type	Auxiliary contact block	
Device Short Name	LA1	
Range Compatibility	TeSys K LC1K TeSys K CA2K TeSys K CA3K	
Mounting Location	Front	
Pole Contact Composition	2 NO + 2 NC	
Contacts Operation	Instantaneous	
[Ue] Rated Operational Voltage	690 V AC 25400 Hz	
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A (at 50 °C)	
Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5 JIS C8201-5-1	
Product Certifications	CB Scheme CCC UL CSA CE UKCA	

## Complementary

Irms Rated Making Capacity	110 A at <= 690 V AC conforming to IEC 60947	
Permissible Short-Time Rating	80 A 1 s	
	60 A 500 ms	
	110 A 100 ms	
Associated Fuse Rating	10 A gG at <= 690 V conforming to IEC 60947	
Minimum Switching Current	5 mA	
Minimum Switching Voltage	17 V	
Non Overlap Distance	0.5 mm	
Insulation Resistance	ce > 10 MOhm	
Connections - Terminals	Spring terminals 1 cable(s) 0.751.5 mm²flexible without cable end Spring terminals 1 cable(s) 0.751.5 mm²figid	

Life Is On Schneider 17 May 2024

Height	30 mm
Width	38 mm
Depth	35 mm
Net Weight	0.045 kg

## **Environment**

Environmental Characteristic	Normal environment	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Protective Treatment	TC conforming to IEC 60068	
Ambient Air Temperature For Storage	-5080 °C	
Ambient Air Temperature For Operation	-2550 °C	
Operating Altitude	2000 m	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	3.900 cm	
Package 1 Width	4.000 cm	
Package 1 Length	4.000 cm	
Package 1 Weight	44.000 g	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	10	
Package 2 Height	4.000 cm	
Package 2 Width	18.000 cm	
Package 2 Length	17.000 cm	
Package 2 Weight	446.000 g	
Unit Type Of Package 3	S02	
Number Of Units In Package 3	100	
Package 3 Height	15.000 cm	
Package 3 Width	30.000 cm	
Package 3 Length	40.000 cm	
Package 3 Weight	4.927 kg	



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations