Product datasheet

Specifications





current transformer tropicalised 1000 5 double output for bars 32x65

METSECT5DA100

Main

Range	PowerLogic	
Product Name	СТ	
Product Or Component Type	Current transformer	
Secondary Current	5 A	
Accuracy Class	Class 0.5 at 15 VA Class 1 at 20 VA	
[In] Rated Current	1000 A	

Complementary

Tropicalised for busbar
1000/5
60 kA
2.5 lth
5
< 720 V AC 50/60 Hz
3 kV
Insulated locking screw
Busbar
Outside: 90 mm Inner: 65 mm
Outside: 94 mm Inner: 32 mm
Frame : 40 mm Total : 87 mm
0.606 kg
3 KV
Class B
65 x 32
With

Environment

Standards

VDE 0414 IEC 61869-2

Product Certifications	CE EAC
Ip Degree Of Protection	IP20
Relative Humidity	095 %
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.3 cm
Package 1 Width	9.5 cm
Package 1 Length	10.1 cm
Package 1 Weight	564.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.143 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins