Product datasheet

Specification





current transformer tropicalised DIN mount 150 5 cables d. 27 - bars 10x32 15x25

METSECT5MA015

Main

Range	PowerLogic
Product Name	СТ
Product Or Component Type	Current transformer
Secondary Current	5 A
Accuracy Class	Class 0.5 at 3 VA Class 1 at 5 VA
[In] Rated Current	150 A

Complementary

Current Transformer Type	Tropicalised for busbar and cable	
Current Transformer Ratio	150/5	
[Ith] Conventional Free Air Thermal Current	9 kA	
Dynamic Withstand Current	2.5 lth	
Maximum Safety Factor	5	
[Ue] Rated Operational Voltage	< 720 V AC 50/60 Hz	
[Ui] Rated Insulation Voltage	3 kV	
Mounting Mode	Insulated locking screw	
Mounting Support	DIN rail Mounting plate Busbar	
Width	Outside: 56 mm	
Height	Outside: 80 mm	
Depth	Frame : 43 mm Total : 63 mm	
Diameter	27 mm	
Net Weight	0.298 kg	
[Uimp] Rated Impulse Withstand Voltage	3 kV	
Electrical Insulation Class	Class B	
Cable Outer Diameter	27 mm	
Opening Of Bars	32.5 x 10.5 25.5 x 15.5	
Sealing	Without	

Environment

Standards	VDE 0414 IEC 61869-2
Product Certifications	EAC CE
Ip Degree Of Protection	IP20
Relative Humidity	095 %
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	7 cm
Package 1 Length	9.2 cm
Package 1 Weight	304 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	35
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	11.053 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins