Product datasheet

Specification





Airing grille cut-out diameter 38mm IP45

NSYCAG38LP

Main

Range	ClimaSys	
Product	ClimaSys CA	
Range Compatibility	Thalassa Thalassa PLS Thalassa Thalassa PLM Thalassa Thalassa TBS	
Product Or Component Type	Plastic ventilation louvre	
Accessory / Separate Part Category	Thermal management accessory	
Accessory / Separate Part Destination	ClimaSys ventilation system	
Fixing Mode	By screws	
Device Composition	2 plastic louvre	

Complementary

Material	Polyamide 6
Colour	Grey (RAL 7032)
Cut-Out Dimensions	38 mm
Height	External: 63 mm
Width	External: 63 mm
Depth	15 mm thread:
Ip Degree Of Protection	IP45

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	10.0 cm
Package 1 Length	11.0 cm
Package 1 Weight	58.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	200
Package 2 Height	40.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm

Package 2 Weight	12.282 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1600
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	97 cm
Package 3 Weight	111 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations