

Product datasheet

Specifications



ClimaSys heating resistance ventil. 250W, 230V aluminium

NSYCR250W230VV

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater with fan
Range Compatibility	Prisma P Prisma G
Power Range	250 W
Input Voltage	230 V AC 50/60 Hz

Complementary

Operating Position	Vertical
Ambient Air Temperature For Operation	-40...70 °C
Ip Degree Of Protection	IP20
Product Certifications	VDE UL
Material	Body: extruded aluminium
Height	200 mm
Width	100 mm
Depth	100 mm
Condition Of Use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed
Fixing Mode	By clips
Mounting Support	35 mm DIN rail

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	11.500 cm
Package 1 Length	21.500 cm
Package 1 Weight	1.104 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6

Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	7.283 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	24
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	41.132 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile No need of specific recycling operations