Product datasheet

Specification





Spacial CRN plain door with mount.plate. H300xW300xD200 IP66 IK10 RAL7035..

NSYCRN33200P

Main

| Range | Spacial |
|-----------------------------|--|
| Product Name | Spacial CRN |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 300 mm |
| Enclosure Nominal Width | 300 mm |
| Enclosure Nominal Depth | 200 mm |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 1 cable gland plate 1 door with lock 1 mounting plate |
| Door Type | Plain |
| Mounting Plate Description | Plain |

Complementary

| Body Type | Back welded with double profile forming a protected sealed area Sides made from a single folded section |
|-----------------------------|---|
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 mm double-bar lock |
| Type Of Gland Plate | Standard |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Cable gland plate by screws Mounting plate by fixing element |
| Material | Enclosure: steel Mounting plate: galvanised steel |
| Surface Finish | Enclosure: epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | cUL UL DNV-GL |
| Net Weight | 5.87 kg |

Environment

| Ip Degree Of Protection | IP66 conforming to IEC 60529 | |
|-------------------------|------------------------------|--|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 | |

Packing Units

| r adming dimes | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 22.0 cm |
| Package 1 Width | 32.0 cm |
| Package 1 Length | 32.0 cm |
| Package 1 Weight | 5.87 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 96 |
| Package 2 Height | 120 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 208 cm |
| Package 2 Weight | 586 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |