# **Product datasheet**

Specification





# Spacial CRN plain door with mount.plate. H600xW400xD250 IP66 IK10 RAL7035..

NSYCRN64250P

#### Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	600 mm
Enclosure Nominal Width	400 mm
Enclosure Nominal Depth	250 mm
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 cable gland plate 1 door with lock 1 mounting plate
Door Type	Plain
Mounting Plate Description	Plain

### Complementary

Body Type	Sides made from a single folded section  Back welded with double profile forming a protected sealed area
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure: steel Mounting plate: galvanised steel
Surface Finish	Enclosure: epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035)
Standards	IEC 62208
Product Certifications	cUL UL DNV-GL
Net Weight	13.811 kg

### **Environment**

Ip Degree Of Protection	IP66 conforming to IEC 60529	
Ik Degree Of Protection	IK10 conforming to IEC 62262	

## **Packing Units**

r adming dimes	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.000 cm
Package 1 Width	40.500 cm
Package 1 Length	61.000 cm
Package 1 Weight	13.741 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	27
Package 2 Height	197.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	384.007 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations