## **Product datasheet**

Specification





# Spacial CRNG dbl plain door w/o mount.plate. H1200xW1000xD300 IP55 IK10 RAL7035

NSYCRNG1210300D

#### Main

Range	Spacial
Product Name	Spacial CRNG
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1200 mm
Enclosure Nominal Width	1000 mm
Enclosure Nominal Depth	300 mm
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 lock 2 cable gland plate: bottom 2 door
Door Type	Plain
Mounting Plate Description	Without mounting plate

### Complementary

Body Type	Single piece body
Number Of Doors	Front face: 2 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 5 mm double-bar
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body: steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	cUL UL
Net Weight	56 kg

#### **Environment**

Ip Degree Of Protection IP55 conforming to IEC 60529

Ik Degree Of Protection IK10 conforming to IEC 62262

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.5 cm
Package 1 Width	101.0 cm
Package 1 Length	122.0 cm
Package 1 Weight	56.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	116.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	127.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations