



# reversible internal door polyester 2 locks grid pattern forPLM64

NSYPAP64G

### Main

| Range                                 | Thalassa                          |
|---------------------------------------|-----------------------------------|
| Accessory / Separate Part<br>Category | Enclosure accessory               |
| Product Or Component Type             | Door                              |
| Application                           | Multi-purpose                     |
| For Enclosure Nominal Dimensions      | -                                 |
| Mounting Location                     | Front side                        |
| Range Compatibility                   | Thalassa Thalassa PLM             |
| Device Composition                    | 1 door 1 handle 4 fixing brackets |

## Complementary

| Material          | Polyester charged with fibreglass  |
|-------------------|--|
| Colour            | Grey (RAL 7035)  |
| Lock Type         | Lock 5 mm double bar   |
| Number Of Locks   | 2  |
| Door Type         | Internal plain   |
| Door Opening Side | Reversible (110 °)   |
| Height            | Grid pattern: 515 mm   |
| Width             | Grid pattern: 305 mm   |
| Depth             | 32 mm available depth between enclosure door: 194 mm available depth between rear: |

## **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 5.000 cm  |
| Package 1 Width              | 37.000 cm |
| Package 1 Length             | 60.500 cm |
| Package 1 Weight             | 1.881 kg  |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 5         |
| Package 2 Height             | 29.000 cm |

| Package 2 Width              | 38.500 cm  |
|------------------------------|------------|
| Package 2 Length             | 61.000 cm  |
| Package 2 Weight             | 9.510 kg   |
| Unit Type Of Package 3       | P12        |
| Number Of Units In Package 3 | 20         |
| Package 3 Height             | 90.000 cm  |
| Package 3 Width              | 80.000 cm  |
| Package 3 Length             | 120.000 cm |
| Package 3 Weight             | 49.620 kg  |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |