Product datasheet

Specifications





Floor standing polyester enclosure, Thalassa PLA, plain door, completely sealed, 1000x750x320mm, IP65, IK10

NSYPLA1073G

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLA
Nominal Height	1000 mm
Nominal Width	750 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door

Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	4 points lock, 5 mm double-bar
Accessibility For Operation	Rear Front
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
Nema Degree Of Protection	NEMA 5 NEMA 1 NEMA 2 NEMA 3X NEMA 3 NEMA 3 NEMA 12 NEMA 13

Product Certifications	Veritas UL/cUL listed DNV Marine
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529 (completely sealed)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.000 cm
Package 1 Width	77.000 cm
Package 1 Length	102.000 cm
Package 1 Weight	17.944 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	3
Package 2 Height	120.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	66.832 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations