Product datasheet

Specification





Floor standing polyester enclosure, Thalassa PLA, plain door, completely sealed, 1250x1000x320mm, IP65, IK10

NSYPLA12103G

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLA
Nominal Height	1250 mm
Nominal Width	1000 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel

Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (120 °)
Lock Type	4 points lock, 5 mm double-bar
Accessibility For Operation	Rear Front
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
Nema Degree Of Protection	NEMA 12 NEMA 2 NEMA 13 NEMA 1
Product Certifications	Veritas DNV Marine UL/cUL listed
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529 (completely sealed)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.500 cm
Package 1 Width	103.000 cm
Package 1 Length	124.000 cm
Package 1 Weight	51.344 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	3
Package 2 Height	160.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	167.032 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations