# **Product datasheet**

Specification





Floor standing polyester enclosure, Thalassa PLA, plain door, completely sealed, 1250x750x320mm, IP65, IK10

NSYPLA1273G

#### Main

Range	Thalassa	
Product Name	Thalassa PLA	
Enclosure Type	Multi-purpose	
Product Or Component Type	Suitable enclosure	
Version	PLA	
Nominal Height	1250 mm	
Nominal Width	750 mm	
Nominal Depth	320 mm	
Enclosure Mounting	Floor-standing	
Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door	

## Complementary

-	
Body Type	Sealed top and bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	4 points lock, 5 mm double-bar
Accessibility For Operation	Rear Front
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
Nema Degree Of Protection	NEMA 2 NEMA 1 NEMA 3 NEMA 12 NEMA 13 NEMA 3S NEMA 5 NEMA 5 NEMA 3X NEMA 3R

Product Certifications	DNV Marine Veritas UL/cUL listed
Electrical Insulation Class	Class II

## **Environment**

Ip Degree Of Protection	IP65 conforming to IEC 60529 (completely sealed)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	126.0 cm
Package 1 Width	38.0 cm
Package 1 Length	78.0 cm
Package 1 Weight	33.5 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	3
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	139 cm
Package 2 Weight	113 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations