Product datasheet

Specification





Wall mounted ABS + PC enclosure, Thalassa PLM, plain door, 310x215x160mm, IP66, IK10, RAL 7035

NSYPLM32G

Main

| Range | Thalassa |
|--------------------|----------------------------|
| Product Name | Thalassa PLM |
| Device Short Name | PLM |
| Enclosure Type | Multi-purpose |
| Category | Compact enclosure |
| Nominal Height | 310 mm |
| Nominal Width | 215 mm |
| Nominal Depth | 160 mm |
| Enclosure Mounting | Wall mounted |
| Device Composition | 1 body 1 door 1 lock |
| Door Type | Plain |
| Lock Type | 3 mm double-bar lock |

Complementary

| Number Of Locks | 1 |
|-----------------------------|---|
| Mounting Plate Description | Without mounting plate |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges |
| Material | ABS + PC |
| Colour | Grey (RAL 7035) |
| Standards | NEMA classification 4X IEC 62208 NEMA classification 13 |
| Electrical Insulation Class | Class II |

Environment

| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
|---------------------------------------|--------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Fire Resistance | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For Operation | -4080 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 22 cm |
| Package 1 Width | 18.01 cm |
| Package 1 Length | 32 cm |
| Package 1 Weight | 1.45 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 70 |
| Package 2 Height | 129 cm |
| Package 2 Width | 80 cm |
| Package 2 Length | 120 cm |
| Package 2 Weight | 111 kg |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |