Product datasheet

Specifications





Wall mounted polyester enclosure, Thalassa PLM, glazed door, with handle, 430x330x200mm, IP66, IK08, RAL 7035

NSYPLM43TVG

Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	430 mm
Nominal Width	330 mm
Nominal Depth	200 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 door 1 handle lock
Door Type	Transparent
Lock Type	3 points lock, handle with 1242E key lock

Complementary

Number Of Locks	1
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body: polyester reinforced with fibreglass Door: tempered glass
Colour	Grey (RAL 7035)
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Operation	-4080 °C

Packing Units

Unit Type Of Package 1

PCE

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	23.0 cm
Package 1 Width	35.0 cm
Package 1 Length	46.0 cm
Package 1 Weight	6.305 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	50
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	188 cm
Package 2 Weight	335 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations