Product datasheet

Specifications





SPACIAL S3X stainless 304L, Scotch Brite® finish, H300xW250xD150 mm.

NSYS3X302515

Main

Range	Spacial	
Product Name	Spacial S3X	
Enclosure Type	Multi-purpose	
Category	Compact enclosure	
Nominal Height	300 mm	
Nominal Width	250 mm	
Nominal Depth	150 mm	
Product Installation	Wall-mounting	
Device Composition	1 body 1 lock: door 1 door	

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail	
Door Type	Plain	
Number Of Doors	Front face: 1 door(s)	
Door Opening Side	Reversible (120 °)	
Lock Type	3 mm double-bar lock	
Mounting Plate Description	Without mounting plate	
Type Of Gland Plate	Without gland plate	
Accessibility For Operation	Front	
Removable Parts	Door by hinges	
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel	
Surface Finish	Body and door: Scotch-Brite® brushed Lock: chromium plated	
Net Weight	3.53 kg	

Environment

Standards	IEC 62208	
Product Certifications	UL 508 type A CAN/CSA 22	
Ip Degree Of Protection	IP66 conforming to IEC 60529	

lk	Degree	Of	Protection
----	--------	----	------------

IK10 conforming to IEC 62262

Environmental Characteristic Sp

Specific hygiene Corrosive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32 cm
Package 1 Width	26.01 cm
Package 1 Length	16.51 cm
Package 1 Weight	3.53 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	147
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	200 cm
Package 2 Weight	460 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	No need of specific recycling operations		