Product datasheet

Specification





SPACIAL S3X stainless 304L, Scotch Brite® finish, H400xW300xD150 mm.

NSYS3X4315

Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	400 mm
Nominal Width	300 mm
Nominal Depth	150 mm
Product Installation	Wall-mounting
Device Composition	1 body
	1 lock: door
	1 door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Plain
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface Finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net Weight	5 kg

Environment

Standards	IEC 62208
Product Certifications	UL 508 type A CAN/CSA 22
Ip Degree Of Protection	IP66 conforming to IEC 60529

Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Corrosive Specific hygiene

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.0 cm
Package 1 Width	31.5 cm
Package 1 Length	42.0 cm
Package 1 Weight	5.0 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	78
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	182 cm
Package 2 Weight	412 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations