Product datasheet

Specifications





SPACIAL S3X stainless 304L, Scotch Brite® finish, H600xW600xD250 mm.

NSYS3X6625

Main

| Range | Spacial |
|----------------------|---|
| Product Name | Spacial S3X |
| Enclosure Type | Multi-purpose |
| Category | Compact enclosure |
| Nominal Height | 600 mm |
| Nominal Width | 600 mm |
| Nominal Depth | 250 mm |
| Product Installation | Wall-mounting |
| Device Composition | 1 body 1 door 2 lock: door 2 perforated vertical profile drilled: door |

Complementary

| • • | |
|-----------------------------|--|
| Body Type | Single piece body, cross-shaped structure Gutter shaped front rail |
| Door Type | Plain |
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 2 points lock, 3 mm double-bar |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Without gland plate |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges |
| Material | Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel |
| Surface Finish | Body and door: Scotch-Brite® brushed Lock: chromium plated |
| Net Weight | 13.902 kg |

Environment

| Standards | IEC 62208 |
|------------------------|-----------------------------|
| Product Certifications | UL 508 type A CAN/CSA 22 |

| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
|------------------------------|-------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Environmental Characteristic | Corrosive Specific hygiene |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 26.5 cm |
| Package 1 Width | 61.0 cm |
| Package 1 Length | 61.5 cm |
| Package 1 Weight | 13.902 kg |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 18 |
| Package 2 Height | 198.0 cm |
| Package 2 Width | 100.0 cm |
| Package 2 Length | 122.0 cm |
| Package 2 Weight | 271.0 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |