# **Product datasheet**

Specifications





# Post fixing device galvanized steel post diam. max 215mm load 100kg for PLM43

NSYSFP300

#### Main

Range	Thalassa
Accessory / Separate Part Category	Fixing accessory
Product Or Component Type	Post fixing device
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 430 mm W: 330 mm D: 200 mm
Mounting Location	Outdoor installations on a post Rear of enclosure
Range Compatibility	Thalassa Thalassa PLM
Device Composition	fixing elements 2 support rail 2 strip

#### Complementary

Material	Galvanised steel
Fixing Mode	By fixing element - on a post location
Permanent Permissible Load	100 kg
Height	45 mm
Width	295 mm
Depth	32.5 mm
Diameter	215 mm

### **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	20.0 cm
Package 1 Length	32.0 cm
Package 1 Weight	1.687 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	32.0 cm
Package 2 Width	42.5 cm
Package 2 Length	10.0 cm

Package 2 Weight	17.583 kg
Unit Type Of Package 3	РАМ
Number Of Units In Package 3	100
Package 3 Height	120 cm
Package 3 Width	100 cm
Package 3 Length	90 cm
Package 3 Weight	330 kg

#### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations