

# Product datasheet

Specifications



Cover plate, Linergy TR, 4 points,  
2.2mm width, for spring terminals  
NSYTRR44, grey, Set of 50

NSYTRACR44

## Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Cover plate
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRR spring terminal terminal block, length = 87 mm
Thickness	2.2 mm

## Complementary

Cable Cross Section	4 mm <sup>2</sup>
Number Of Connections	4
Number Of Measurement Input	2
Quantity Per Set	Set of 50
Net Weight	3 g
Colour	Grey

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	13.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	50
Package 2 Height	5.0 cm
Package 2 Width	13.0 cm
Package 2 Length	17.0 cm
Package 2 Weight	170.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	600

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	2.411 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	