



PratiKa wander socket - straight -32 A - 3P + N + E - 380...415 V AC - IP44

PKF32M435

### Main

Range	Mureva
Product Or Component Type	Wander socket
Device Short Name	Mureva screw
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	380415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Captive screws
Cable Cross Section	2.510 mm²
Cable Outer Diameter	11.521 mm
Cable Entry	Cable gland Fair lead
Thread Type	Pg 21
Net Weight	0.3 kg
Height	106 mm
Width	106 mm
Depth	172 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

#### **Environment**

IFC 60309-2	
120 00000 Z	
IEC 60300-1	
	IEC 60309-2

Ip Degree Of Protection	IP44 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-1
Relative Humidity	50 % at 40 °C 70 % at 30 °C
	90 % at 20 °C
Ambient Air Temperature For	35 °C ( 86400 s )
Operation	-2540 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	11.000 cm
Package 1 Length	18.000 cm
Package 1 Weight	279.200 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	17.500 cm
Package 2 Width	26.500 cm
Package 2 Length	26.500 cm
Package 2 Weight	2.390 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	16
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.211 kg

# **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
<b>Environmental Disclosure</b>	Product Environmental Profile
Circularity Profile	No need of specific recycling operations