Product datasheet

Specifications





socket, Harmony Electromechanical Relays, for RXM2LB relays, 7A, screw clamp socket, mixed contact terminal

RXZE1M2C

Main

| Range Of Product | Harmony Electromechanical Relays | |
|-------------------------------|--------------------------------------|--|
| Device Short Name | me RXZ | |
| Product Or Component Type | Socket | |
| Product Compatibility | Plug-in relay RXM with 2 C/O contact | |
| Contacts Type And Composition | n 2 C/O | |
| [Ith] Conventional Free Air | 7 A | |

Complementary

| [Ue] Rated Operational Voltage | 250 V | |
|--|--|--|
| Contact Terminal Arrangement | Mixed | |
| Connections - Terminals | Screw clamp terminals, 1 x 0.21 x 1.0 mm² (AWG 24AWG 17) flexible with cable end Screw clamp terminals, 2 x 0.22 x 1.0 mm² (AWG 24AWG 17) flexible with cable end Screw clamp terminals, 1 x 0.51 x 1.5 mm² (AWG 20AWG 16) solid without cable end | |
| | Screw clamp terminals, 2 x 0.52 x 1.5 mm² (AWG 20AWG 16) solid without cable end | |
| Tightening Torque | < 0.8 N.m for M3 screw(s) | |
| Fixing Mode | By screw (panel) Clip-on (35 mm symmetrical DIN rail) | |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV | |
| Overvoltage Category | III | |
| Pollution Degree | 3 | |
| Sale Per Indivisible Quantity | 10 | |
| Width | 22.5 mm | |
| Net Weight | 0.034 kg | |

Environment

| Dielectric Strength | 2500 V |
|---------------------------------------|-----------|
| Standards | IEC 61984 |
| Marking | CE |
| Ambient Air Temperature For Storage | -5585 °C |
| Ambient Air Temperature For Operation | -4055 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.2 cm |
| Package 1 Width | 3.1 cm |
| Package 1 Length | 7.5 cm |
| Package 1 Weight | 0.03 kg |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 6.4 cm |
| Package 2 Width | 7.9 cm |
| Package 2 Length | 11.2 cm |
| Package 2 Weight | 0.38 kg |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 180 |
| Package 3 Height | 15 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 7.1 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ② | Toxic Heavy Metal Free | |
| Ø | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |


Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |

RXZE1M2C

Dimensions Drawings

Dimensions



RXZE1M2C

Connections and Schema

Wiring Diagram

