


Product datasheet

Specifications



CANopen cordset - molded female SUB-D9 connectors - standard - IP20 - 5 m

TSXCANCADD5

 **Discontinued on:** 30 Jun 2023

 **Discontinued**

Main

Range Of Product	CANopen
Bus Type	CANopen
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / Separate Part Destination	CANopen bus
Cable Length	5 m

Complementary

Electrical Connection	2 female connectors SUB-D 9 pin(s)
Marking	CE
Net Weight	0.44 kg

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	21.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	449.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.49 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration