



20A 440V Wheatherproof Surface Mount Double Pole Isolating Switch IP66

WHD20_GY

Main

Range	Kavacha
Product Or Component Type	Isolating switch
Device Short Name	W
Device Application	Control

Complementary

[le] Rated Operational Current	20 A at 440 V AC-22A
Poles Description	2P
Motor Rating	M180
Width	82 mm
Height	170 mm
Depth	90 mm

Environment

Ip Degree Of Protection	IP66
Standards	IEC 60947-3
Environmental Characteristic	Weatherproof

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	9 cm
Package 1 Length	8.3 cm
Package 1 Weight	733.333 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	36.5 cm
Package 2 Width	28.5 cm
Package 2 Length	43.5 cm
Package 2 Weight	22000 g
Unit Type Of Package 3	P12

Number Of Units In Package 3	540
Package 3 Height	130 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	414000 a



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations