

Product datasheet

Specifications



booted head for pushbutton XAC-B -
green - 16 mm, -25..+70 °C

XACB9213

Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACB
Marking	Unmarked
Operator Additional Information	Booted
Operating Travel	16 mm
Cap/Operator Or Lens Colour	Green
Product Compatibility	XESD1291 XESD1281 XESD1181 XESD1191
Sale Per Indivisible Quantity	10

Complementary

Net Weight	0.005 kg
------------	----------

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 EN 60947-5-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	4.0 cm
Package 1 Length	8.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	7.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	8.0 cm
Package 2 Width	4.0 cm
Package 2 Length	8.0 cm
Package 2 Weight	72.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	