Product datasheet

Specifications





Empty control station, Harmony XALD, XALK, plastic, dark grey lid, light grey base, 2 cut out, UL CSA certified

XALD02H7

Main

Range Of Product	Harmony XALD	
Product Or Component Type	Empty control station	
Device Short Name	XALD	
Product Destination	For XB5 Ø 22 mm control and signalling units 2 cut-outs	
Number Of Cut-Out		
Colour Of Base Of Enclosure	Light grey (RAL 7035)	
Colour Of Cover	Dark grey (RAL 7016)	
Material	Polycarbonate	
Cable Entry	2 knock-outs for cable entry, clamping capacity: 14 mm 2 knock-outs for Pg 13 cable gland and ISO M20, clamping capacity: 12 mm	
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K	

Complementary

Group Of Product	UL-CSA grey
Main Group	2 cut-outs
	SR1
	MR1
	PR1
	PF1
	PF2
	SR2
	SF1
	MF2
Electrical Composition Code	SF2 MF1
	Front mounting
Mounting Of Block	Rear mounting
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m
Net Weight	0.205 kg
Number Of Vertical Rows	2
Number Of Horizontal Rows	1
Assembly Style	For customer assembly

Environment

Protective Treatment

ΤН

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C
Overvoltage Category	Class II conforming to IEC 60536
Nema Degree Of Protection	NEMA 13 NEMA 4X
Ik Degree Of Protection	IK03 conforming to EN 50102
Standards	JIS C8201-5-1 EN/IEC 60947-5-5 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-1 UL 508 EN/IEC 60947-5-4 JIS C8201-1
Product Certifications	UL CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	7.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	191.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.33 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Dimensions



(1) 2 knock-outs for Pg 13.5 cable gland, maximum capacity 12 mm/0.47 in.
(2) Knock-out for cable entry, maximum capacity 14 mm/0.55 in.

Control station fitted with:	c in mm	c in in.
Flush pushbutton	62	2.44
Pilot light	64	2.52
Illuminated pushbutton	65.5	2.58
Projecting pushbutton	66	2.60
Selector switch	80	3.15
Mushroom head pushbutton	91.5	3.58
Latching mushroom head Emergency stop pushbutton wit h key	115	4.53
Key switch	105.5	4.15