

Product datasheet

Specifications



hour counter - mechanical 7 digit display - 115 V AC

XBKH70000001M

⚠ Discontinued on: 4 Jul 2022

⚠ Discontinued

Main

Range Of Product	Zelio Count
Product Or Component Type	Hour counter
Display Type	Mechanical
Size	48 x 48 mm
Display Digits	7 digit(s)
Reset	Without
Technology Type	Electromechanical

Complementary

[Us] Rated Supply Voltage	115 V AC 50 Hz Us +/- 10 %
Power Consumption In Va	0.56 VA
Backup Time	Permanent
Counting Mode	Adding 1/100 of an hour
Time Range	0...99 999.99 h
Input Function	Enable
Input Type	Contact
Mounting Mode	Flush-mounted
Mounting Support	Panel mounting
Fixing Mode	By self-locking clamp
Connections - Terminals	Screw terminal block
Height	48 mm
Net Weight	0.06 kg
Width	48 mm
Character Size	5 mm

Environment

Standards	EN 50082-2 EN 50081-2 VDE 0435
Product Certifications	UR
Ip Degree Of Protection	IP65 conforming to EN/IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-10...50 °C
Ambient Air Temperature For Storage	-25...70 °C
Vibration Resistance	3 gn (f= 10...150 Hz) conforming to EN/IEC 60068-2-6
Shock Resistance	30 gn for 11 ms conforming to EN/IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to EN/IEC 60536

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.8 cm
Package 1 Width	17.8 cm
Package 1 Length	9.2 cm
Package 1 Weight	116 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance


 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings


Electromechanical and Electronic Totalizing Timers

Timers with Mechanical Display

XBKH7000000•M




Flush-Mounting



Timers with LCD Display

XBKH81000033E



Flush-Mounting

