Product datasheet

Specifications





Rotating beacon, Harmony XVR, 130mm, orange, without buzzer, 24V DC

XVR13B05

Main

Range Of Product	Harmony XVR
Product Or Component Type	Prewired rotating mirror beacon
Sound Signalling	Without
Device Short Name	XVR
Mounting Diameter	130 mm
Ip Degree Of Protection	IP66 (resistant to vibration) conforming to IEC 60529
[Us] Rated Supply Voltage	24 V DC
Light Source	High luminosity LED, orange

Complementary

· · · · · · · · · · · · · · · · · ·		
Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe	
Cad Overall Width	130 mm	
Cad Overall Depth	130 mm	
Net Weight	0.8 kg	
Marking	CE	
Product Mounting	By 3 M8 screws	
Supply Voltage Limits	1930 V DC	
[Uimp] Rated Impulse Withstand Voltage	0.8 kV	
Current Consumption	125 mA	
Flashing Frequency	2.7 Hz	
Clamping Connection Capacity	1.25 mm ²	
Awg Gauge	AWG 18	
Cable Length	400 mm	

Environment

Standards	IEC 61000-6-2
	IEC 61000-6-4
Protective Treatment	тс
Ambient Air Temperature For Storage	-3570 °C
Ambient Air Temperature For Operation	-3050 °C

Electrical Shock Protection Class Class II conforming to IEC 61140

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26.5 cm
Package 1 Width	18.8 cm
Package 1 Length	18.8 cm
Package 1 Weight	1.218 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.438 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings

Rotating Mirror Beacon

Dimensions





Product datasheet

Mounting and Clearance

Rotating Mirror Beacon

Panel Cut-out

