

Product datasheet

Specifications



charger for remote device, Harmony eXLhoist, standard

ZARC01

Main

Range Of Product	Harmony eXLhoist
Accessory / Separate Part Type	Battery charger
Accessory / Separate Part Category	Electrical accessory

Complementary

[Us] Rated Supply Voltage	100...240 V AC
Network Frequency	50...60 Hz
Nominal Output Current	0.9 A at 90 V AC
Connections - Terminals	5-position plug-in connector
Net Weight	0.26 kg

Environment

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-20...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	7.500 cm
Package 1 Length	14.000 cm
Package 1 Weight	283.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.072 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins