

Product datasheet

Specifications



Powerpact 4 - panelboard - 250A - 13 ways - 3P - Style C

Local distributor code:
387298658 MG2C13

EAN Code: 3606485858777

Main

Range	PowerPact
Product Or Component Type	Panelboard
Product Name	PowerPacT 4
Device Application	Distribution
Colour	Cream (RAL 9001)
Provided Equipment	removable bottom gland plate end cover

Complementary

[In] Rated Current	250 A
Number Of Ways	13 ways (3P)
[Ue] Rated Operational Voltage	415 V 50 Hz AC
Breaking Capacity	36 kA AC 1 s
Enclosure Material	epoxy-polyester powder steel
Thickness	Cover: 1.2 mm Enclosure: 1.6 mm
Cable Entry	Bottom entry at main
Device Mounting	Wall mounted
Height	1074 mm
Width	850 mm
Depth	260 mm
Horizontal Fixing Centres	670 mm
Vertical Fixing Centres	920 mm

Environment

Ip Degree Of Protection	IP3x
Standards	BS EN 61439-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27 cm
Package 1 Width	90 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	112 cm
Package 1 Weight	60 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations