Product datasheet

Specification





Powerpact 4 - panelboard - 800A - 12 ways - 3P - Style E - top cable entry

Local distributor code: 387299136

MG8C12T

EAN Code: 3606487056843

Main

Range	PowerPact	
Product Or Component Type	Panelboard	
Product Name	PowerPacT 4	
Device Application	Distribution	
Colour	Cream (RAL 9001)	
Provided Equipment	removable bottom gland plate end cover	

Complementary

[In] Rated Current	800 A	
Number Of Ways	12 ways (3P)	
	36 ways (1P)	
[Ue] Rated Operational Voltage	415 V 50 Hz AC	
Breaking Capacity	50 kA AC 1 s	
Enclosure Material	epoxy-polyester powder steel	
Cable Entry	Top entry at main	
Device Mounting	Wall mounted	
Height	1896 mm	
Width	850 mm	
Depth	260 mm	

Environment

Ip Degree Of Protection	IP3x	
Standards	BS EN 60439-1	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	41 cm
Package 1 Width	180 cm
Package 1 Length	140 cm
Package 1 Weight	105 kg

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations