


Product datasheet

Specifications



Acti9 IsoBar A P - pan assembly - 14 ways SP+N

Local distributor code:
405639050

SEA9APN14PS

EAN Code: 3606489484330

Main

Range	Acti9
Product Or Component Type	Pan assembly
Device Application	Distribution

Complementary

[In] Rated Current	125 A
Number Of Ways	14 ways - 1P + N
Incomer Device Options	Switch disconnecter - 2P Terminal block - 2P RCCB - 2P
Protection Device Options At Outgoer	Miniature circuit breaker (MCB) 63 A max Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A max
Height	262 mm
Width	374 mm
Depth	87 mm
Busbar Pitch	18 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	30.0 cm
Package 1 Length	39.0 cm
Package 1 Weight	1.961 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information