Product datasheet

Specifications





Acti9 Isobar B - pan assembly - 12 ways TP&N Local distributor code:

396793021

SEA9BN12PS

EAN Code: 5018934962320

Main

Range	Acti9	
Product Or Component Type	Pan assembly	
Device Application	Distribution	

Complementary

Range Compatibility	Acti 9 Acti9 Isobar B distribution board	
Incomer Device Options	2P switch disconnector 2P terminal block 2P RCCB	
Protection Device Options At Outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max	
Number Of Ways	12 ways - 3P + N	
Busbar Pitch	18 mm	
Length	th 324 mm	

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.4 cm
Package 1 Width	22.0 cm
Package 1 Length	40.5 cm
Package 1 Weight	1.87 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	100
Package 2 Height	112.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	251.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information	Yes
Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations